



Rev.	Description	Initiator	Date
07	Updated to include IP68 version	RKC	12/3/2008



- NOTES:
1. Material: Stainless Steel
 2. Tool and mounting adapters have M3 tapped holes and 3mm dowel pin holes for interfacing
 3. **WARNING: DO NOT LOOSEN OR REMOVE INTERFACE PLATES DUE TO POTENTIAL DAMAGE**

NOTES: UNLESS OTHERWISE SPECIFIED
 DO NOT SCALE DRAWING. DRAWN IN SOLIDWORKS.
 ALL DIMENSIONS ARE IN MILLIMETERS.



1031 Goodworth Drive, Apex, NC 27539, USA
 Tel: +1.919.772.0115 Email: info@ati-ia.com
 Fax: +1.919.772.8259 www.ati-ia.com
 ISO 9001 Registered Company

DRAWN BY: Dan Norton 12/2/05	TITLE IP65/IP68 Nano25 Transducer w/ Axial Cable Exit		
CHECKED BY: Penny Fusco 3/16/07	SCALE 2.5:1	SIZE B	DRAWING NUMBER 9230-05-1259-07
WEIGHT LBS: 0.21	PRODUCT RELEASE # 051201-2		DATE: SHEET 1 OF 1
ASSEMBLY REF:			