


Rev.	Description	Initiator	Date
03	ECO 14323: Increased tolerance on dowel hole positions from ±.013 to ±.025	SZJ	3/28/2016




- Notes:
1. Material: Stainless Steel.
  2. Tool and Mounting Adapters have M3 tapped holes and 3mm dowel pin holes for interfacing.
  3. **WARNING: DO NOT LOOSEN OR REMOVE INTERFACE PLATES DUE TO POTENTIAL DAMAGE.**
  4. Standard connector (not shown) has 17mm diameter & is 67.5mm long.
  5. Cable is IP65/IP68 rated only at transducer end.

NOTES: UNLESS OTHERWISE SPECIFIED.  
DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN MILLIMETERS.



1031 Goodworth Drive, Apex, NC 27539, USA  
Tel: +1.919.772.0115 Email: info@ati-ia.com  
Fax: +1.919.772.8259 www.ati-ia.com  
ISO 9001 Registered Company

PROPERTY OF ATI INDUSTRIAL AUTOMATION, INC. NOT TO BE REPRODUCED IN ANY MANNER EXCEPT ON ORDER OR WITH PRIOR WRITTEN AUTHORIZATION OF ATI.



DRAWN BY: R. Chambers 3/9/12		TITLE	
CHECKED BY: J. Walser 3/9/12		IP65/IP68 Mini40 Transducer	
PROJECT # 110516-2	SHEET 1 OF 1	SCALE 3:2	SIZE B
		DRAWING NUMBER 9230-05-1421	REVISION 03