




3X M3 SFHCS			itial Drawing Safety S 4-pin M 9005-20 Note 1,	Switch and Connector 12 Eurofast 0-1165	/2014
3X M3 SFHCS			/ 9005-20	D-1165	
7.4 12.7 - 25.4			4X M5 SHCS 242 / 50 in-lbs Note 3	3X M5 SFHCS -242 / 50 in-lbs Note 3	
	TEM NO. QTY. 1 1	PART NUMBER 9120-TSL-SS-8074	DESCRIPTION	- Vertical Hooks, No Trip Do	
SPE DC ALL	OTES: UNLESS OTHERWISE PECIFIED. O NOT SCALE DRAWING. LL DIMENSIONS ARE IN ILLIMETERS.		1031 Goodwol Tel: +1.919.77 Fax: +1.919.77 ISO 9001 Reg PROPERTY OF ATI INDUSTRIAL	rth Drive, Apex, NC 27539, USA 2.0115 Email: info@ati-ia.com	ANY
ue. que value.		DRAWN BY: J. Winterroth, 2/2 CHECKED BY: D. Norton, 2/24/1		/ - Vertical Hooks, No Trip Do	















							I	1
		Rev. 01	Descriptic Initial Drav				Initiator JMW	Date 02/21/2014
				wing .				02/21/2014
				4X M5 SI 242 / 50 I Note 3	in-lbs	∑—242 Note	M5 SFHCS / 50 in-lbs	
ITEM NO. QTY. PART NU							Jooks No Ti	
NOTES: UNLESS C		9120-10L-00-0	501-		Own	· · · · · · · · · · · · · · · · · · ·		· •
NOTES: UNLESS OTHERWISE SPECIFIED. DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN MILLIMETERS. 1031 Goodworth Drive, Apex, NC 27539, USA Tel: +1.919.772.0115 Email: info@ati-ia.com ISO 9001 Registered Company PROPERTY OF ATI INDUSTRIAL AUTOMATION, INC. NOT TO BE REPRODUCED IN ANY MANNER EXCEPT ON ORDER OR WITH PRIOR WRITEN AUTHORIZATION OF ATI.							UCED IN ANY	
	F	DRAWN BY: J. Winterrot	h, 2/21/14	TITLE				
\bigoplus		CHECKED BY: D. Norton, 2	2/24/14		I Swi	DRAWING NUMBER	Hooks, No T	rip Dog REVISION
3rd ANG	LE PROJECTION	PROJECT # -	SHEET 1 OF 2	1:2	В	9630-20-TSL-SS-8074		01

Notes:


- Fasteners and switch shipped loose. To be installed by customer.
 Customer to install pre-applied fasteners and torque to listed torque values.
 Customer to use Loctite or similar thread locker and torque to listed torque.
 Customer to orient switch arm as needed.



4 (Black)--M12x1.0 -3 (Blue) 1 (Brown) 2 (White)


Face View Part #1510-1313006-04 4-Pin Male Eurofast Receptacle

<u>Pin #:</u>	<u>Wire Color</u>	<u>Contact Type</u> (Group)	Internal switch <u>#:</u>	
Pin 1	Brown	N.O.(Pin 1 & 4)	13	
Pin 2	White	N.O. (Pin 2 & 3)	33	
Pin 3	Blue	N.O. (Pin 2 & 3)	34	
Pin 4	Black	N.O.(Pin 1 & 4)	14	



Initiator	Date
-	-

Wiring Diagram (switch not actuated)





PROPERTY OF ATI INDUSTRIAL AUTOMATION, INC. NOT TO BE REPRODUCED IN ANY MANNER EXCEPT ON ORDER OR WITH PRIOR WRITTEN AUTHORIZATION OF ATI.

TSL TSI Switch Assembly - Vertical Hooks, No Trip Dog

SIZE	DRAWING NUMBER	REVISION
В	9630-20-TSL-SS-8074	01