





Rev.	Description	Initiator	Date
04	EC10640: Ad Net System details to the drawing	JW	02/05/2013



- Notes:**
1. Material: Stainless Steel
 2. Sensing Reference Frame Origin at surface center of Tool Adapter.
 3. Do not disassemble transducer. Doing so could damage transducer and will void warranty.
 4. For best accuracy, transducer must be mounted to surfaces rigid enough to support loads without deflection.
 5. Cable must be connected to transducer to maintain proper seal.
 6. Cable is IP68 rated only at transducer end. Transducer is IP68 rated in freshwater environment at a depth of up to 10 meters.

NOTES: UNLESS OTHERWISE SPECIFIED.
DO NOT SCALE DRAWING. ALL DIMENSIONS ARE IN MILLIMETERS.

ATI INDUSTRIAL AUTOMATION

1031 Goodworth Drive, Apex, NC 27539, USA
Tel: +1.919.772.0115 Email: info@ati-ia.com
Fax: +1.919.772.8259 www.ati-ia.com
ISO 9001 Registered Company

PROPERTY OF ATI INDUSTRIAL AUTOMATION, INC. NOT TO BE REPRODUCED IN ANY MANNER EXCEPT ON ORDER OR WITH PRIOR WRITTEN AUTHORIZATION OF ATI.

DRAWN BY: P.Sparrow, 2/16/06
CHECKED BY: D. Norton 2/17/06

PROJECT # SHEET 1 OF 1

TITLE: IP68-10m THETA Transducer

SCALE	SIZE	DRAWING NUMBER	REVISION
1:1.5	B	9230-05-1273	04

3rd ANGLE PROJECTION