



NOTES:


1. MATERIAL: Stainless Steel
2. Sensing Reference frame origin at surface center of tool adapter.
3. Do not disassemble transducer. Doing so could damage transducer and void warranty.
4. For best accuracy, transducer must be mounted to surfaces rigid enough to support loads without deflection.
5. Cable must be connected to Transducer to maintain proper seal.
6. Cable is only IP68 rated at Transducer End. Transducer is IP68 rated in freshwater environment at a depth of up to 10 meters.



ISOMETRIC VIEW



SIDE VIEW



TOOL SIDE

NOTES: UNLESS OTHERWISE SPECIFIED	
DO NOT SCALE DRAWING. DRAWN IN SOLIDWORKS. ALL DIMENSIONS ARE IN MILLIMETERS.	
3rd ANGLE PROJECTION	
DRAWN BY: P.Sparrow, 2/16/06	TITLE
CHECKED BY: D. Norton, 2/17/06	IP68-10m OMEGA160 Transducer
WEIGHT LBS: 16	SCALE 1:1.5
ASSEMBLY REF:	SIZE B
	DRAWING NUMBER 9230-05-1274-02
	PRODUCT RELEASE #
	DATE:



1031 Goodworth Drive, Apex, NC 27539, USA
Tel: +1.919.772.0115 Email: info@ati-ia.com
Fax: +1.919.772.8259 www.ati-ia.com
ISO 9001 Registered Company

IP68-10m OMEGA160 Transducer
9230-05-1274-02
SHEET 1 OF 1